




## 6.2 Guida articolazione

### 6.2.1 Lato cerniera T

#### 6.2.1.1 Sicurezza base - RC 1 N



									N°
J	J	290 – 410	300	120	150	–	–	Roto Sil	787345 <input type="checkbox"/>
		411 – 600	490	190	250	–	–	Roto Sil	787346 <input type="checkbox"/>
		601 – 800	690	200	350	–	–	Roto Sil	787347 <input type="checkbox"/>
		801 – 1000	890	200	500	–	–	Roto Sil	787348 <input type="checkbox"/>
			890	200	500	1	E	Roto Sil	788617 <input type="checkbox"/>
		1001 – 1200	1090	200	500	–	–	Roto Sil	787350 <input type="checkbox"/>
			1090	200	500	1	E	Roto Sil	787349 <input type="checkbox"/>
1201 – 1400	1290	200	500	1	E	Roto Sil	787351 <input type="checkbox"/>		



#### INFORMAZIONI

Da LBB 1400 mm è necessaria la forbice secondaria.

#### 6.2.1.2 Sicurezza - RC 2 / RC 2 N



									N°
J	J	801 – 1000	890	200	500	1	V	Roto Sil	787360 <input type="checkbox"/>
		1001 – 1200	1090	200	500	1	V	Roto Sil	787361 <input type="checkbox"/>
		1201 – 1400	1290	200	500	1	V	Roto Sil	787362 <input type="checkbox"/>